



**RBT-2000D-50**  
2000 kVA / 1600 kW

# ROTARY UPS

## RBT-2000D-50

### Performances and Characteristics

Voltage	3 x 400V
Frequency	50 Hz
Nominal phase current	2887 A
Nominal apparent power	2000 kVA
Nominal active power	1600 kW
Nominal cos φ	0.93 leading to 0.8 lagging
Rotabloc Efficiency at nominal load	96.6%
Nominal Autonomy	10s
Maximum autonomy at full load	11.4s
Maximum energy storage	18.2 MJ
Maximum temperature (higher ratings available)	Up to 50° C (1)
Altitude (without de-rating)	≤ 1000 m
Humidity	≤ 90%


### Standard Features

- Automatic lubrication system
- Touch-screen digital HMI
- Dynamic Autonomy Control (DAC)
- Electrical panels IEC 61439 Form 1
- Automatic by-pass

### Options


- Plug & Run parallel working
- Supervision software
- Containerized solution
- Bearing monitoring
- Electrical panels IEC 61439 Form 4
- Medium Voltage
- Soundproof enclosure
- High Temperature 50° C

### ROTABLOC®




L x W x H (2x) 3225 x 1200 x 1570 mm  
 Net weight (2x) 9285 kg  
 Protection IP23

### Control Cabinet



W x D x H 1250 x 650 x 2125 mm  
 Net weight 325 kg  
 Protection IP43

### Power and VFD Cabinets



W x D x H 5750 x 1050 x 2125 mm  
 Net weight 6190 kg  
 Protection IP43

(1): Standard 40°C - Up to 50°C with power derating

All data in this document is for information only and is subject to change.