

ROTARY UPS RBT-2000D-50



Performances and Characteristics

| Voltage | 3 x 400V |
|--|-----------------------------|
| Frequency | 50 Hz |
| Nominal phase current | 2887 A |
| Nominal apparent power | 2000 kVA |
| Nominal active power | 1600 kW |
| Nominal $\cos \phi$ | 0.89 leading to 0.8 lagging |
| Rotabloc Efficiency at nominal load | 96.6% |
| Nominal Autonomy | 10s |
| Maximum autonomy at full load | 11.4s |
| Maximum energy storage | 18.2 MJ |
| Maximum temperature (higher ratings available) | Up to 50° C (1) |
| Altitude (without de-rating) | ≤ 1000 m |
| Humidity | ≤ 90% |

Standard Features


Automatic lubrication system
Touch-screen digital HMI
Dynamic Autonomy Control (DAC)
Electrical panels IEC 61439 Form 1
Automatic by-pass

Options


Plug & Run parallel working
Supervision software
Containerized solution
Bearing monitoring
Electrical panels IEC 61439 Form 4
Medium Voltage
Soundproof enclosure
High Temperature 50° C

Power and VFD Cabinets

ROTABLOC®



Control Cabinet



 $L \times W \times H$ (2x) 3225 x 1200 x 1570 mm Net weight (2x) 9285 kg

Protection IP23

W x D x H 1210 x 510 x 2155 mm Net weight 355 kg

Protection IP43

W x D x H 4470 x 1250 x 2175 mm

Net weight 6210 kg Protection IP43

(1): Standard 40°C - Up to 50°C with power derating

All data in this document is for information only and is subject to change.